ENPULSION

NANO R³

FEEP | FIELD EMISSION FLECTRIC PROPULSION

as of JAN 2024

The ENPULSION NANO R³ is the next-generation FEEP system based on the flight-proven success story that is the ENPULSION NANO. Incorporation of lessons learned from a large number of acceptance test campaigns and in-orbit performance verifications led into an updated electronics design, thermo-structural concept, and software functionality. The resulting product – the ENPULSION NANO R³ – features increased reliability, radiation tolerance, and environmental resilience.





FLIGHT HERITAGE

The ENPULSION NANO R³ is an updated version of the space proven ENPULSION NANO with more than 170 units in space*. It is directly building on its heritage, leveraging the proven design and component selection.

*as per January 2024.



PROTECTIVE CASING

The thruster is assembled into a protective casing that shields the electronics from the hazardous space radiation environment, facilitates handling during integration, and allows side mounting.



RAD-TOLERANT ELECTRONICS

All EEE components of the ENPULSION NANO R³ are procured in lot-controlled batches. Selected sets of these batches are subjected to radiation testing, so that each thruster can be traced back to a fully representative qualification model. EEE components were selected and integrated to be more tolerant to TID and SEE.



VERSATILE PERFORMANCE

Thrust can be controlled through the electrode voltages, providing excellent controllability over the full thrust range and a low thrust noise.

Due to the efficient ionization process, the ENPULSION NANO R³ can provide a higher specific impulse than any other ion propulsion system currently on the market.





SAFE AND INERT SYSTEM

The ENPULSION NANO R³ contains no moving parts and the indium propellant is in its solid state at room temperature. Avoiding any liquid and reactive propellants as well as pressurized tanks significantly simplifies handling, integration, and launch procedures.






PROPERTIES AND PERFORMANCE

While the required power to fire the ENPULSION NANO R^3 starts at around 15 W, at higher power levels one can choose between high-thrust and high-specific-impulse operation. The ENPULSION NANO R^3 can operate at an I_{sp} range of 1,500 to 5,000 s.

At any given thrust point, higher I_{sp} operation will increase the total impulse, while also increasing the power demand. The thruster can be operated along the full dynamic range throughout the mission. This means that high I_{sp} and low I_{sp} maneuvers can be included in a mission planning as well as high-thrust orbit maneuvers and low-thrust precision control maneuvers.



Depending on available power the user can choose from any operational point—data shown is for 12V configuration

DYNAMIC THRUST RANGE:1	10-350 μΝ
NOMINAL THRUST:	350 μΝ
SPECIFIC IMPULSE:	1,500-5,000 s
PROPELLANT MASS:	220 g ±5%
TOTAL IMPULSE:2	MORE THAN 4,000 Ns
POWER AT NOMINAL THRUST:	45 W INCL. NEUTRALIZER
OUTSIDE DIMENSIONS:	98.0 × 99.0 × 95.3 mm
MASS (DRY/WET):	1180g (DRY)/<1400g (WET)
TOTAL SYSTEM POWER:	15-45 W
HOT STANDBY POWER:3	4 – 7 W
COMMAND INTERFACE:	RS422/RS485
SUPPLY VOLTAGE: (OTHER VOLTAGES UPON REQUEST)	12 V, 28 V

EMITTER SELECTION SERVICE

Since the company was founded in 2016 we have delivered hundreds of thrusters to customers worldwide, close to 200 of which are currently in space. Therefore we have developed an empirical understanding of the intrinsic variation of the performance and parameters of emitters in these thrusters in their production process and in their application in different types of missions.

This enables us, to offer our customers our new Emitter Selection Service which allows you to select between two distinct types of crown emitters:

- \triangleright Alpha (α) emitters provide the best balance between price, performance, and fastest delivery times. This is the perfect solution for commercial constellation applications.
- SAMMA (γ) emitters are hand-picked for their peak performance and especially appropriate for your missions in deep space, exploration, and others where emitter output needs to be taken to extremes.

¹ The ENPULSION NANO R³ can be operated at a wide range of thrust and specific impulse, depending on the power level available. The operational envelope is based on total system power including typical heater and neutralizers consumption. Performances shown above correspond to maximum thrust to power curves for different grades of emitters.

² Strongly depends on emitter option. See performance map for selection options

³ Depends on accommodation and resulting thermal environment.